



DATA SHEET

Bench Power Supplies

Order code	Manufacturer code	Description
85-1715	n/a	DUAL RAIL 1A POWER SUPPLY RE

Bench Power Supplies

Page 1 of 3

The enclosed information is believed to be correct. Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.

Revision A
20/02/2007

Sales: 01206 751166
Sales@rapidelec.co.uk

Technical: 01206 835555
Tech@rapidelec.co.uk

Fax: 01206 751188
www.rapidonline.com

Specification**Multi Output Stabilised Supply****Getting Started**

Input	
Supply Voltage	230V a.c.
Supply Frequency	50Hz
Maximum Power	50W
Panel Fuse Rating	2A quick blow
Mains Plug Fuse Rating	3A

Output

Voltage	+/- 5V, 12V, 15V smoothed and regulated d.c.
Maximum Output Current	1A per rail

Electromagnetic Compatibility

The use of this apparatus outside the classroom, laboratory, study area or similar such place invalidated the conformity with the protection requirements of the Electromagnetic Compatibility Directive (89/336/EEC) and could lead to prosecution.

The unit is designed for 240V a.c. 50Hz operation only (a 120V version is available to special order).

Plug in the unit and switch on using the rocker switch on the front panel. If all is correct, the rocker switch should illuminate, showing that the mains is present

Using the Unit

The unit delivers +15V, +12V, +5V, 0V, -5V, -12V and -15V through separate terminals. This configuration provides a large range of voltage combinations in single, symmetrical dual and asymmetrical dual rail operation (see chart below). A maximum of 1A per rail is available. In the case of a short circuit, the particular rail(s) involved will automatically shut down, but other unaffected outputs will continue to supply current.

The outputs are available from colour coded, 4mm terminal posts coloured red for positive, blue for 0V and black for negative.

PROLONGED SHORT CIRCUIT CONDITIONS SHOULD BE AVOIDED.**Single Rail Operation Grid**

Volts	Max Current	red +15	red +12	red +5	blue 0	black -5	black -12	black -15
3	10mA						+	0
5	1A			+	0			
7	10mA					+	0	
10	1A		+		0			
12	1A			+		0		
15	1A				+		0	
17	1A				+		0	
20	1A				+		0	
24	1A				+		0	
27	1A				+		0	
30	1A	+						0

Dual Rail Operation Grid

Suggested Use

Volts	Current	red	red	red	blue	black	black	black
5-0-5	1A+1A	+15	+12	+5	0	-5	-12	-15
10-0-10	1A+10mA		+	0	-			
12-0-12	1A+1A	+	0	0	0	-	-	-
15-0-15	1A+1A	+	0	0	0	0	0	0
17-0-3	1A+10mA		+	+	0	0	0	0
24-0-3	1A+10mA	+	+	+	0	0	0	0
27-0-3	1A+10mA	+	0	0	0	0	0	0
7-0-5	10mA+1A	+	0	-				
10-0-5	10mA+1A	+	0	-				
12-0-5	1A+1A	+	0	-				
15-0-5	1A+1A	+	0	-				
3-0-7	10mA+10mA	+	0	-				
5-0-7	1A+10mA		+	+	0	0	0	0
10-0-7	1A+10mA		+	+	0	0	0	0
17-0-7	1A+10mA	+	+	+	0	0	0	0
20-0-7	1A+10mA	+	0	-	0	0	0	0
5-0-10	1A+10mA		+	+	0	0	0	0
17-0-10	1A+10mA	+	+	0	0	0	0	0
20-0-10	1A+10mA	+	0	-	0	0	0	0
3-0-12	10mA+1A	+	0	-				
5-0-12	1A+1A		+	0	-			
15-0-12	1A+1A	+	0	-				
5-0-15	1A+1A		+	0	-			
12-0-15	1A+1A	+	0	-				
7-0-17	10mA+1A	+	0	-				
10-0-17	10mA+1A	+	0	-				
7-0-20	10mA+1A	+	0	-				
10-0-20	10mA+1A	+	0	-				
3-0-34	10mA+1A	+	0	-				
3-0-27	10mA+1A	+	0	-				

Key

- +
-
- 0

positive voltage output
negative voltage output
zero volts reference point

The unit is designed for powering all types of electronic circuits including transistor, CMOS, TTS, linear integrated circuits and power amplifiers (within the power output range of the unit). The range voltages present offer opportunities for demonstrating clipping due to asymmetrical power supply rails etc.

Fusing

The unit is protected by a 2A quick blow fuse. The fuse is mounted in a tamperproof fuse holder on the back panel.

Should the unit's mains neon not light when the unit is switched on, then proceed as follows:

1. Unplug the unit from the mains.
2. Check the mains plug fuse - this should be replaced with a 3A fuse.
3. Unscrew the fuse holder and inspect the fuse. Replace if necessary.

Electrical Safety Testing

The unit is classified as Class 1 for the purposes of safety testing. Suitable earth test points are the two metal ends of the handle or the feet securing screws on the underside. For further details on safety testing, please refer to Health and Safety Executive leaflet GS23 (ISBN 0 11 883567 X).